



# Mobility Zone

## Invacare Softform Premier



### Unique Features

### Benefits

<b>Deep contoured Insert pad for enhanced pressure care area</b>	Maximises body contact area and optimises pressure reduction
<b>Cover fabric conforms to deep contoured foam castellations on the upper surface of the Insert pad when mattress is profiled</b>	Minimizes rucking of cover fabric on top surface, reducing potential for tissue damage
<b>Suitable for High Risk patients / Very High Risk when used in conjunction with a profiling bed</b>	Can contribute significantly to pressure ulcer prevention
<b>No need to turn over</b>	Reduces manual handling issues
<b>Single piece foam 'U' core</b>	Facilitates patient transfer by providing effective side-wall support
<b>Double-coated poly-urethane sides</b>	Reduces the risk of strike through, hydrolysis or delamination
<b>Two way stretch polyurethane waterproof cover</b>	Provides excellent recovery and durability and helps reduce shear and friction forces
<b>High frequency welded seams and zip</b>	Reduces risk of fluid ingress
<b>Full length waterfall flap conceals the zip</b>	Further risk reduction of fluid ingress (through zip)
<b>Toughened PU coated base</b>	Prolongs longevity of the mattress
<b>Water penetration resistance</b>	35 kPa minimum (BS 3424: part 26). 35 kPa minimum after 20,000 cycles Martindale Abrasion Test EN ISO 5470-2

CODE	DESCRIPTION	TOTAL LENGTH	TOTAL WIDTH	TOTAL HEIGHT	SWL	UNIT WEIGHT
SPM197/88	Invacare Softform Premier	1970mm	880mm	152mm	247.6KG	14 Kg